

## 牌号规格

## 主要用途

牌号规格	粘度 mPa·S	醇解度 mol%	有效含量 %	灰份 % (Na <sub>2</sub> O)	甲醇含量 %	pH	纤维及纺织			造纸					粘合剂					特殊用途											
							经线上浆	防水涂层	PVA水溶纤维	熔融纺丝	玻纤上浆	表面施胶	热敏纸	离型/防油纸	喷绘相纸	水溶纸	医疗纸	其他特种纸	高耐水白乳胶	高速纸品胶	低VOC粘合剂	VAE/PVAc聚合	偏光片	拼板胶	水溶性热熔胶	特种粘合剂	PVB树脂及薄膜	电子/精密陶瓷	化妆品	电液液	水溶薄膜
Anol AF-03	3.0-3.8	98.0-99.0	≥94	≤0.4	≤1%	5.0-7.0		☆														★	☆		★						★
Anol AF-05	5.0-6.0	98.0-99.0	≥94	≤0.4	≤1%	5.0-7.0					★	★	★						☆				☆	★	☆				★		
Anol AF-17	24.0-31.0	98.0-99.0	≥94	≤0.4	≤1%	5.0-7.0	★	★	★		★	★	★	★				★				☆	★	☆				★			
Anol AP-03	3.2-3.7	87.0-89.0	≥97	≤0.3	≤0.8%	5.0-7.0				☆		★						☆	☆			★		☆			○		★		
Anol 5-88 ◎	4.5-5.5	86.5-89.0	≥97	≤0.3	≤0.8%	5.0-7.0	★	★	★		★		☆						☆	☆			★				○	★			
Anol 5-88 DF	4.5-5.5	86.5-89.0	≥97	≤0.3	≤0.8%	5.0-7.0	★	★			★		★									☆	☆	★			○	★			
Anol 5-88 DL	4.5-5.5	86.5-89.0	≥97	≤0.15	≤0.8%	5.0-7.0	★	★			★		★									☆	★				○	★			
Anol AP-17*	20.0-25.0	87.0-89.0	≥97	≤0.3	≤0.8%	5.0-7.0	★	★	★		☆							☆	☆			★	★	★		☆	★				
Anol AP-17 DF	20.0-25.0	87.0-89.0	≥97	≤0.3	≤0.8%	5.0-7.0	★	★			☆								☆			☆	★			☆	★				
Anol AP-24	40.0-48.0	87.0-89.0	≥97	≤0.3	≤0.8%	5.0-7.0					☆											☆	★			☆	★				
Anol AP-35	80.0-115.0	87.0-98.0	≥97	≤0.3	≤0.8%	5.0-7.0	★	★					★	★				★	★	★		☆	★	★					★		
Anol 22-85*	20.0-24.0	84.0-86.0	≥97	≤0.3	≤0.8%	5.0-7.0	★	★			☆							★	★		★	★	☆	★	★		★	★			
Anol AL-03	2.7-3.4	80.0-82.0	≥97	≤0.3	≤0.8%	5.0-7.0																									
Anol 5-80 ◎	4.5-6.0	80.0-82.0	≥97	≤0.3	≤0.8%	5.0-7.0	☆	☆	★	★	★																				
Anol 5-80 DL	4.5-6.0	80.0-82.0	≥97	≤0.15	≤0.8%	5.0-7.0																									
Anol AL-24 *	44.0-52.0	80.0-82.0	≥97	≤0.3	≤0.8%	5.0-7.0	☆	☆	★	★	★																				
Anol 6-73	5.0-7.0	71.5-73.5	≥97	≤0.3	≤0.8%	5.0-7.0																									
Anol 2-87 S	2.2-2.8	86.5-89.0	≥95	≤0.3	≤0.8%	5.0-7.0							★																		
Anol 13-99 CL	11.0~14.0	99.0-99.6	≥95	≤0.3	≤0.8%	3.5~5.0																									
Anol 21-93 CL	19.0~24.0	92.0~94.0	≥95	≤0.3	≤0.8%	3.5~5.0																									
Anol 4-98 E	3.4-4.8	98.0-99.0	≥94	≤0.4	≤1%	5.0-7.0			★	★			★																		
Anol 27-93 E	22.0-30.0	98.0-99.0	≥94	≤0.4	≤1%	5.0-7.0																									
Anol 28-98 E	24.0-30.0	98.0-99.0	≥94	≤0.4	≤1%	5.0-7.0																									
Anol 25-88 CK	20.0-30.0	85.0-90.0	≥96	≤0.7	≤0.8%	5.0-7.0	★	★																							

注：  
 \* 表示有低甲醇型号，甲醇含量可低至0.3%，如需更低甲醇要求，请咨询我司。  
 ◎ 表示有低灰分型号，灰分含量可低至0.1%，如有更低灰分要求，可咨询我司。

★ 特别适用  
 ☆ 适用  
 ○ 推荐尝试